BOWMAN® Dispensers Organize · Contain · Comply

# **BD004–0012** Large Capacity Bottle Dispenser Stand



#### **Product Description:**

#### • Kit Includes:

- BW004-0512 Bottle Holder 1 Gallon
  - Holds one gallon of hand sanitizer
  - Quartz Beige Powder-Coated Aluminum
- KS010-0412 Floor Stand
- Quartz Beige Powder-Coated Steel
- Assembly hardware included

Primary Area for Product Usage:

- All ports of entry
- · Anywhere respiratory hygiene products are needed

#### Dispenses:

 Bottles no larger than 13.00"H x 6.50" diameter (16.5 cm x 8.82 cm)

**Product Specifications** (overall assembled dimensions):

- 17.00"W x 41.51"H x 17.00"D (43.2 cm x 105.4 cm x 43.2 cm)
- 15.2 lbs (6.9 kg) approximated

#### Package Specifications:

- Package Quantity: 1 per case
- 36"L x 20"W x 6"H (91.4 cm x 50.8 cm x 15.2 cm)
- 18.0 lbs (8.2 kg) approximated





## **BD004–0012** Large Capacity Bottle Dispenser Stand Assembly Instructions

Assembly

Always mount dispensers securely prior to loading with product.



To secure base to column, turn column upside down (with top plate down) and place base inverted, as shown, on column.



Turn stand right side up, so the base is on the floor.



Use Phillips screwdriver to secure base to column with (4x) screws  $(10-32 \times 5/16")$ .



Attach the BW004-0512 Bottle Holder to the column using (4x) screws included with stand. Tighten.

Hardware

• (8x) 10-32 x 5/16" Phillips head screws

٠



Bottles can be secured with a zip-tie or cable from the handle to the top ring, if added security is needed.

#### Parts included:

- Base
- Column
- Bottle Holder 1 Gallon

#### Tools Required:

- Phillips Screwdriver
- Flathead Screwdriver

BD004-0012 - Assembly

Information subject to change without notice. Dimensions are approximate. (Not to scale) 800.962.4660 • www.Bowma ©2020 BOWMAN® Dispensers, LLC. All Rights Reserved. Product specifications subject to change without notification. Consumables not included. BD00400127DSa

BOWMAN Dispensers 20325 71<sup>st</sup> Ave NE, Suite D, Arlington, WA 98223 800.962.4660 • www.BowmanDispensers.com



# **BD004–0012** Large Capacity Bottle Dispenser Stand

**Characteristics & Care** 

### BW004-0512

Powder-Coated Aluminum

## KS010-0412

Powder-Coated Steel

#### **Material Characteristic**

**Designed for Long-Term Use** 

Our powder-coated aluminum dispensers resist corrosion, chipping, and flaking. It is lightweight, yet high in strength. This material will provide longlasting products that hold up well, even in tough environments.

Powder-coated aluminum is ideal for dispensers used in a healthcare or industrial settings. It is impact resistant and is not affected by extremes in temperature.

Dispensers made of powder-coated aluminum are clean, bright, and attractive, creating a professional appearance.

**Designed for Long-Term Use** 

Our steel dispensers and stands are coated with polyester powders which makes them highly resistant to corrosion.

Powder-coated steel is ideal for dispensers used in a healthcare or an industrial setting because it is impact resistant and is not affected by extremes in temperature.

Dispensers and stands made of powder-coated steel are both attractive and functional, providing years of service.

#### **Care and Cleaning**

For best results, clean by washing the surface with a diluted solution of a mild, non-abrasive detergent in cold or warm water and a non-abrasive cloth. Standard hospital cleaning supplies can be used.

Dry with a soft cloth. Do not use any solvent-based materials, abrasives (e.g. Scotch-brite, steel wool), or apply excessive force during cleaning.