



Related Products (each sold separately):

• MB-600 - Door Hanger - Standard (shown below)



Product Description:

- Hanger Door Long
- Holds BOWMAN® protection systems
- Hooks over the top of a door with a thickness no greater than 2.44"
- · Quartz Beige Powder-Coated Steel

Primary Area for Product Usage:

 Anywhere a door hanger is needed to mount a BOWMAN® dispenser for personal protection equipment


Package Specifications:


- Package Quantity: 12 per case
- 21"W x 14"H x 10"D (53.3cm x 35.6cm x 25.4cm)
- 19.00 lbs (8.6kg) approximated

Product Specifications (overall external dimensions):

- 5.50"W x 19.00"H x 2.50"D (14.0cm x 48.3cm x 6.4cm)
- 1.4 lb (0.6kg) approximated

Mounting Specifications:





Proper Hanging Procedure:

- Attach hanger securely back of hanger must lay flush against surface
- 2) Hang empty dispenser on hanger.
- 3) Load product in dispenser.
- 4) To remove, reverse order of steps.

Installation

Care and Construction

Powder-Coated Steel

Material Characteristics


Designed for Long-Term, Heavy-Duty Applications

Dispensers and stands made of powder-coated steel are both attractive and functional, providing years of service. Our powder-coated steel dispensers and stands provide long-lasting products that hold up well in tough environments.

Powder-coated steel is ideal for dispensers used in a healthcare or an industrial setting. It is impact resistant and is not effected by extremes in temperature.

Mount hanger to door before attaching a dispenser. Top of hanger MUST lay flush with top of door. Door thickness cannot exceed 2.44".

Always mount dispensers securely prior to loading with product.



Parts included:

Dispenser

Tools Required:

No tools required to assemble dispenser

Care and Cleaning

The powder-coated finish resists common chemicals and cleaning agents and can be easily wiped clean with soap and water.